



Geheugenkaart voor easy500/700, 32kB

Type EASY-M-32K
Catalog No. 270884

Leveringsprogramma

Toepasbaar voor		easy500 easy 700
geheugenomvang	kByte	32 k module
Information relevant for export to North America		
Product Standards IEC/EN see Technical Data; UL 508; CSA C22.2 No. 142-M1987; CSA C22.2 No. 213-M1987; CE marking		
UL File No. E135462		
UL Category Control No. NRAQ		
CSA File No. 012528		
CSA Class No. 2252-01 + 2258-02		
North America Certification UL listed, CSA certified		
Degree of Protection IEC: IP20, UL/CSA Type: -		

Ontwerpverificatie conform IEC/EN 61439

Technische gegevens ontwerpverificatie		
Bedrijfsomgevingstemperatuur min.	°C	-25
Bedrijfsomgevingstemperatuur max.	°C	55

Technische gegevens ETIM 7.0

PLC's (EG000024) / PLC geheugenkaart (EC000192)		
Elektro-, automatiserings- en procesbesturingstechniek / Besturing / Programmeerbare logische besturing (pLC) / PLC-geheugeneenheid (ecl@ss10.0.1-27-24-22-12 [AKE535014])		
Geheugentype		Overig
Geheugenomvang	Kilobyte	32

Goedkeuringen

Product Standards		IEC/EN see Technical Data; UL 508; CSA C22.2 No. 142-M1987; CSA C22.2 No. 213-M1987; CE marking
UL File No.		E135462
UL Category Control No.		NRAQ
CSA File No.		012528
CSA Class No.		2252-01 + 2258-02
North America Certification		UL listed, CSA certified
Degree of Protection		IEC: IP20, UL/CSA Type: -

Overige productinformatie (links)

Montagehandleiding Stuurrelais easy IL05013015Z (AWA2528-2105)	
Montagehandleiding Stuurrelais easy IL05013015Z (AWA2528-2105)	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL05013015Z2018_02.pdf
Handboek Stuurrelais easy500, easy700 MN05013003Z (AWB2528-1508)	
Handbuch „Stuurrelais easy500, easy700“ MN05013003Z (AWB2528-1508) - Deutsch	ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/MN05013003Z_DE.pdf
Manual "easy500, easy700 control relays" MN05013003Z (AWB2528-1508) - English	ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/MN05013003Z_EN.pdf