



Powering Business Worldwide

Verbindliche Bestellangaben für beliebige Taster-Leuchtmelder-Kombinationen
Mandatory ordering data for push button-indicator lamp combinations
Commande obligatoire de combinaisons de boutons et de voyants lumineux

Auftrags-Nr. Ordering number N° de commande		Position Position Poste		Büro Office Bureau		Bearbeiter Referee Employé	
Kundenspez.-Nr. Customer specific no. N° client spécifié		Kunde Customer Client				Datum Date Date	


Lage der Einbaustellen / Position of locating places / Disposition des perçages

M22-COMBINATION-...


RMQ-Titan

Menge ☐ horizontal ☐


vertikal ☐



M22-IY1 ☐
M22-I1 ☐
M22-I2 ☐
M22-I3 ☐
M22-I4 ☐
M22-I6 ☐



Elektronik-Leiterplatte für Busfähigkeit / Printed circuit for systems communication / Carte de circuits imprimés électroniques pour raccordement au bus
AS-Interface (AS-I)



Einbaustelle Locating plate Emplacement	Frontelement Front element Bouton	Tastenplatte/Linse Plate/Lense Étiquette/Lentille	Schildträger Carrier plate Plastron	Einlegeschild Insert plate Étiquette	Funktionselement/ Kontaktkonfiguration: Anordnung nach EN 50 013 Function component/ Contact configuration according to EN 50 013 Bloc de fonction/ Disposition des contacts selon EN 50 013
A	...mm/	...mm/			
B	...mm/	...mm/			
C	...mm/	...mm/			
D	...mm/	...mm/			
E	...mm/	...mm/			
F	...mm/	...mm/			

RMQ-...ASI
Ein-, Ausgangskonfiguration
Input-, Output configuration
Configuration d'entrée/sortie

I/Q-Code, ID-Code: 7.0 – Slave-Adress: 0 – 31 (Default = 0)

data bit D0	INPUT	I1 →	OUTPUT	Q1 →
data bit D1		I2 →		Q2 →
data bit D2		I3 →		Q3 →
data bit D3		I4 →		Q4 →

IEC 447, EN 60 447

USA / CANADA